




EXISTING (REMOVED)		INSTALL	
	80 PSI PRESSURE		80 PSI PRESSURE
	100 PSI PRESSURE		100 PSI PRESSURE
	150 PSI PRESSURE		150 PSI PRESSURE
	200 PSI PRESSURE		200 PSI PRESSURE
	250 PSI PRESSURE		250 PSI PRESSURE
	300 PSI PRESSURE		300 PSI PRESSURE
	350 PSI PRESSURE		350 PSI PRESSURE
	400 PSI PRESSURE		400 PSI PRESSURE
	450 PSI PRESSURE		450 PSI PRESSURE
	500 PSI PRESSURE		500 PSI PRESSURE
	550 PSI PRESSURE		550 PSI PRESSURE
	600 PSI PRESSURE		600 PSI PRESSURE
	650 PSI PRESSURE		650 PSI PRESSURE
	700 PSI PRESSURE		700 PSI PRESSURE
	750 PSI PRESSURE		750 PSI PRESSURE
	800 PSI PRESSURE		800 PSI PRESSURE
	850 PSI PRESSURE		850 PSI PRESSURE
	900 PSI PRESSURE		900 PSI PRESSURE
	950 PSI PRESSURE		950 PSI PRESSURE
	1000 PSI PRESSURE		1000 PSI PRESSURE



TYPE	SIZE	PLANT	LOCATION	REMARKS
AVB	0.5	Chicago Faucet 892	No plant I.D. # - Hose reel - decontamination room at emergency entrance	
AVB	0.375	Chicago Faucet 892	Depend tube below breakroom sink - east of GVN #6	
AVB	0.375	Chicago Faucet L-100	Sink - isolation room #17	
AVB	0.375	Chicago Faucet 892	Sink - isolation room #17	
AVB	0.75	Chicago Faucet 892	Sink - isolation room #17	

PROJ. MGR.

CAD. MGR.

CAD. DWG.

F.L.D. CHK.

F.L.D. DWG.

HDI. JOB #

PREVIOUS SURVEY

PROJ. MGR.

CAD. MGR.

CAD. DWG.

F.L.D. CHK.

F.L.D. DWG.

HDI. JOB #

PREVIOUS SURVEY

PROJ. MGR.

CAD. MGR.

CAD. DWG.

F.L.D. CHK.

F.L.D. DWG.

HDI. JOB #

PREVIOUS SURVEY

PROJ. MGR.

CAD. MGR.

CAD. DWG.

F.L.D. CHK.

F.L.D. DWG.

HDI. JOB #

PREVIOUS SURVEY

PROJ. MGR.

CAD. MGR.

CAD. DWG.

F.L.D. CHK.

F.L.D. DWG.

HDI. JOB #

PREVIOUS SURVEY

PROJ. MGR.

CAD. MGR.

CAD. DWG.

F.L.D. CHK.

F.L.D. DWG.

HDI. JOB #

HOSPITAL & MEDICAL FACILITY

CITY, STATE

GROUND FLOOR

CROSS CONNECTION CONTROL SURVEY

SHEET NUMBER: M-3

